

### Features

- Shift+® Square multifunction handshower offers full coverage and targeted massage spray options
- 8" (203 mm) Honesty® rainhead with a full coverage spray and an adjustable ball joint for precise spray adjustment
- 2.5 gpm (9.5 lpm) maximum flow rate
- Handshower contains flow-regulating check valve for backflow prevention
- Awaken® wall-mount supply elbow with check valve
- Right-angle shower arm and flange
- 24" (610 mm) sidebar length offers a custom shower at various heights
- Box includes: 8" rainhead, rainhead arm, handshower, 60" metal shower hose, adjustable sidebar with handshower mounting bracket, wall-mount supply elbow, and Rite-Temp valve trim
- Valve sold separately

### Material

- Premium material construction with metal handle ensures reliability and durability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Wall-mount

### Required Products/Accessories

K-11748 Series Rite-Temp® Valves

### Included Components

K-10124 Right-angle Shower Arm and Flange  
K-21336 Square two-function handshower, 2.5 gpm  
K-26148 8" single-function rainhead, 2.5 gpm  
K-9514 60" Shower Hose  
K-98341 27" sidebar  
K-98351 wall-mount supply elbow with check valve  
K-T99762-4 Rite-Temp® valve trim with push-button diverter



### Codes/Standards



ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992



### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass



### Technical Information

All product dimensions are nominal.

#### Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

#### Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

### Notes

Install this product according to the installation guide.