

Statement®

Iconic single-function handshower, 2.5 gpm K-26286

Features

- Single-function handshower delivers a full, consistent spray, regardless of water pressure
- Infinity provides three spray experiences in one: strongrinsing (top), massaging (middle), and broad coverage (lower)
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface for maximum performance
- 2.5 gpm (9.5 lpm) maximum flow rate at 45 psi (3.1 bar)

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- 1/2 -14 NPT connection
- Requires shower hose (sold separately)
- Bracket or slidebar required for wall-mount installation
- Deck-mount holder required for deck-mount installation

Recommended Products/Accessories

K-9514 60" Shower Hose K-8593 72" Shower Hose K-26309 Wall-mount handshower holder K-26310 Wall-mount handshower holder with supply elbow and check valve K-26312 32-1/8" slidebar K-26313 40" slidebar K-26314 32" deluxe slidebar with integrated water supply K-23723 Faucet cleaner



Codes/Standards

ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 IAPMO Certification

KOHLER[®] Faucet Lifetime Limited Warrantv

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color Code Description


CP	Polished Chrome
SN	Vibrant® Polished Nickel
AF	Vibrant® French Gold
BN	Vibrant® Brushed Nickel
BV	Vibrant® Brushed Bronze
BL	Matte Black
2MB	Vibrant® Brushed Moderne
тт	Brass Vibrant Titanium



KOHLER, Faucets

Statement® Iconic single-function handshower, 2.5 gpm K-26286





Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum 2.5 gal/min (9.5 l/min) flow:

Notes

For use with automatic compensating valves rated at 1.5 gal/min (5.7 l/min) or less.

