

Features

- Multifunction handshower offers two spray options
- Sweep® spray provides a wide massage stream of fine droplets with moderate pressure
- Cloud spray experience restores with a thick cloud of silky, super-fine water droplets
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup
- Optimized sprayface for maximum performance
- 2.5 gpm (9.5 lpm) maximum flow rate

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- G 1/2 inlet connection
- Requires shower hose (sold separately)
- Requires wand handshower holder or ceiling-mount dual shower arm (sold separately)
- Not recommended for use with a standard handshower holder

Recommended Products/Accessories

- K-23723 Faucet cleaner
- K-26305 Ceiling-mount single-function dual rainhead arm




Codes/Standards

None Applicable

KOHLER India Faucet Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)
Pressure: 45 psi (3.1 bar)