

Features

- Single-function round rainhead features Full Coverage with Katalyst™ air-induction technology, a drenching spray experience ideal for rinsing shampoo from hair
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface for maximum performance
- 2.5 gpm (9.5 lpm) maximum flow rate at 80 psi (5.5 bar)

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- G 1/2 inlet connection
- Requires single-function rainhead shower arm and flange (sold separately)

Recommended Products/Accessories


K-23723 Faucet cleaner
K-26319 3" ceiling-mount single-function rainhead arm and flange
K-26320 6" ceiling-mount single-function rainhead arm and flange
K-26321 12" ceiling-mount single-function rainhead arm and flange
K-26322 15-1/2" wall-mount single-function rainhead arm and flange
K-26307 19" wall-mount single-function rainhead arm and flange

**Codes/Standards**

None Applicable

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

**Technical Information**

All product dimensions are nominal.

Drain included: No

Spout:

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

Notes

For use with automatic compensating valves rated at 2.00 gal/min (7.6 l/min) or less.