

Features

- Single-function round rainhead features Full Coverage with Katalyst technology, a drenching spray experience ideal for rinsing shampoo from hair.
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup.
- Optimized sprayface for maximum performance.
- 1.75 gpm (6.6 lpm) maximum flow rate at 80 psi (5.5 bar).
- G 1/2 connection.

Material

- Premium material construction for durability and reliability.
- KOHLER finishes resist corrosion and tarnishing.

Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray.

Installation

- Requires single-function rainhead shower arm and flange (sold separately).

Water Conservation & Rebates


- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System.

Required Products/Accessories

K-26320W 6" ceiling-mount rainhead arm

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

None Applicable

See website for detailed warranty information.

**Technical Information**

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 1.75 gal/min (6.6 l/min)

Pressure: 80 psi (5.5 bar)