

Features

- Single-function round body spray delivers four twisting Deep Massage streams, targeting sore muscles to ease away aches and pains
- Sprayface on semi-recessed ball joint rotates 20° in any direction for targeted hydromassage
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Low-profile design complements any decor
- 1/2" NPT connection
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System
- 1.75 gpm (6.6 lpm) maximum flow rate at 45 psi (3.1 bar)

Material

- KOHLER® finishes resist corrosion and tarnishing
- Durable material construction

Installation

- Surface-mount with ball-joint recessed into wall

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards










ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
IAPMO Certification


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	TT	Vibrant Titanium
	BGP	Brushed Graphite



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)