Statement®



Oblong Vichy single-function body spray, 1.75 gpm **K-26300-G**

Features

- Oblong single-function linear body spray delivers 14 twirling Deep Massage streams, targeting sore muscles to ease away aches and pains
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Low-profile design complements any decor
- 1.75 gpm (6.6 lpm) maximum flow rate at 45 psi (3.1 bar)
- 1/2" NPT connection
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System

Material

- Durable material construction
- KOHLER® finishes resist corrosion and tarnishing

Installation

Semi-recessed into wall

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards

ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 California Energy Commission (CEC) IAPMO Certification

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes


Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	TT	Vibrant Titanium





Oblong Vichy single-function body spray, 1.75 gpm K-26300-G



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum 0 gal/min (0 l/min)

flow:

Notes

Install this product according to the installation instructions.

