

Features

- Modern, simplistic exposed thermostatic column serves as a hub for bath/shower controls
- Includes bath/shower column, multifunction rainhead, handshower, hose, thermostatic valve and control panel with integrated bath filler
- Dual-function oblong rainhead features Full Coverage with Katalyst technology, a drenching spray experience ideal for rinsing shampoo from hair
- Deep Massage streams twist and swirl, targeting sore muscles to ease away aches and pains
- Multifunction handshower with advanced spray engine provides three spray experiences: Full Coverage with Katalyst technology, Deep Massage, and Cloud
- Cloud spray experience restores with a thick cloud of silky, super-fine water droplets
- 2.5 gpm (9.5 lpm) showerhead and handshower flow rate
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup
- Optimized sprayface for maximum performance
- Slidebar bracket allows you to adjust the height and angle of the handshower
- Mechanically controlled thermostatic mixing valve maintains outlet temperature throughout shower experience
- Control panel includes adjustable temperature dial with integrated adjustable high-temperature limit feature and shower outlet on/off buttons
- When pressed once, shower outlet turns on and button pops out, becoming a knob for water flow adjustment
- When pressed back in, water turns off and outlet button aligns with control plate surface; flow setting remains intact

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- G 1/2 inlet and outlet
- Valve is fully serviceable from control panel



Codes/Standards

ASME A112.18.1/CSA B125.1


KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black



Technical Information

All product dimensions are nominal.

Shower Valve:

Flow Rate (Max) @ 45 psi	5 gal/min (18.9 l/min)
Manufacturer's minimum rated flow:	2.5 gal/min (9.5 l/min)
Pressure:	45 psi (3.1 bar)
Maximum (Static) Pressure:	125 psi (8.6 bar)
Minimum (Operating) Pressure:	20 psi (1.4 bar)

Drain included: No

Handshower:

Rated maximum flow:	2.5 gal/min (9.5 l/min)
Pressure:	80 psi (5.5 bar)

Showerhead/Body Spray:

Rated maximum flow:	2.5 gal/min (9.5 l/min)
Pressure:	80 psi (5.5 bar)

Notes

Install this product according to the installation instructions.

For use with showerheads or handsprays rated at 2.5 gal/min (9.5 l/min) or higher.