

### Features

- Trim plate includes temperature control knob with integrated adjustable high-temperature limit stop and shower outlet on/off buttons
- When pressed once, shower outlet turns on and button pops out, becoming a knob for water flow adjustment
- When pressed back in, water turns off and outlet button aligns with control plate surface; flow setting remains intact
- High-temperature limit setting for added safety
- Low-profile design with easy-to-clean water-resistant casing
- Requires six-port thermostatic valve with integral volume control (sold separately)
- Up to 13.3 gpm (50 lpm) flow rate at 45 psi (3.1 bar) with maximum flow of 10.5 gpm (39.5 lpm) from one outlet

### Installation

- Mounts on finished wall surface





### Codes/Standards

ASME A112.18.1/CSA B125.1

### KOHLER India Faucet Limited Warranty

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.