

Features

- Includes shower column with integrated mixing valve, 10" rainhead, multifunction handshower, hose, handshower holder, and push-button diverter
- Single lever handle allows for both volume and temperature control
- Single-function round rainhead features Full Coverage with Katalyst™ air-induction technology, a drenching spray experience ideal for rinsing shampoo from hair
- Column's push-button diverter easily switches between rainhead and handshower outlets
- Rain Duet™ handshower provides five spray experiences: full coverage, Champagne, massage, full coverage + Champagne, and full coverage + massage
- Thumb tab allows for a smooth transition between sprays
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Includes 60" (1524 mm) smooth hose
- Easy-to-adjust handshower holder slides up/down shower column with left-side release; locks in place at your preferred height
- Cold-water release expels cold water ahead of your next shower, for a warm experience the moment you turn on the faucet
- 2.5 gpm (9.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Part of the Accliv bathroom faucet and showering collection
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

**Codes/Standards**

Plumbing Standards
GB 18145


See website for detailed warranty information.

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall-mount
- G 1/2 inlet connection



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.