

Features

- Painted glass shade perfectly diffuses the light, reducing glare in the bathroom
- Requires bulb with candelabra (E12) base; B10 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Coordinates with other products in the Simplice collection
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall-mount

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards

UL 1598
CSA C22.2 No. 250.0



KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass



Required Electrical Service

One circuit required.

120 V, 0.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Glass, Zinc, Aluminum

Number of Lights: 1

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 1

Shade Type: Frosted Glass

Hanging Type: Non-hanging

Notes

Install this product according to the installation instructions.