

Features

- Seeded glass shade adds a striking design element reminiscent of original flat glass
- Requires bulb with medium (E26) base; type T14 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Coordinates with other products in the Simplicite collection
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Ceiling-mount

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards

UL 1598
CSA C22.2 No. 250.0


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass



Required Electrical Service

One dedicated circuit required.

120 V, 0.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material:	Steel, Glass, Aluminum, Brass
Number of Lights:	1
Lighting Type:	Socket-based
Socket Type:	E-26 Medium
Number of Shades:	1
Shade Type:	Seeded Glass
Hanging Type:	Downrod
Downrod Detail:	1 x 6" (152 mm), 3 x 12" (305 mm)
Height:	29-13/16" (757 mm) - 65-13/16" (1671 mm)