

Features


- Single-function rainhead
- Dual core technology showcases unique synchronized flow of deep core and rain converge spray experiences
- Inner deep core spray creates deluge of intense drenching
- Outer rain converge spray features visually stunning lattice pattern
- Includes key to help remove inner sprayface for easy routine cleaning
- Outer sprayface features MasterClean™, an easy-to-clean surface that withstands mineral buildup
- 5.5 gpm (22 lpm) maximum flow rate at 43.5 psi (3 bar)
- Available in a range of dazzling finishes

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Ceiling- or wall-mount
- Requires rainhead arm and flange (sold separately)



Codes/Standards






None Applicable



KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 5.5 gal/min (20.8 l/min)

Pressure: 45 psi (3.1 bar)

Notes

Install this product according to the installation guide.