

Features

- Single-function rainhead
- Dual core technology showcases unique synchronized flow of deep core and rain converge spray experiences
- Inner deep core spray creates deluge of intense drenching
- Outer rain converge spray features visually stunning lattice pattern
- Includes key to help remove inner sprayface for easy routine cleaning
- Outer sprayface features MasterClean™, an easy-to-clean surface that withstands mineral buildup
- 22.0 lpm (5.5 gpm) maximum flow rate at 3.0 bar (43.5 psi)
- Available in a range of dazzling finishes

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Ceiling- or wall-mount
- Requires rainhead arm and flange (sold separately)

Required Products/Accessories

K-163471N

or

K-163461N 463 mm wall-mount single-function rainhead arm and flange

or

K-224471N

or

K-224461N Round 460 mm wall-mount single-function rainhead arm and flange

or

K-15399T-B 249 mm ceiling-mount rainhead arm and flange



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	RGD	Vibrant Rose Gold
	BRD	Vibrant Brushed Rose Gold



Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 5.5 gal/min (20.8 l/min)

Notes

Install this product according to the installation instructions.