

Features

- Push-button diverter
- Diverter valve code-approved for backflow protection
- Includes hose
- 15 gpm (57 lpm) flow rate using 1/2" high-flow valves
- Handshower sold separately
- Part of the Occasion bathroom faucet and accessory collection

Material

- Brass
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck- or bath-mount

Recommended Products/Accessories

- K-72421-G Three-function handshower, 1.75 gpm
- K-22165-G Four-function handshower, 1.75 gpm
- K-22166-G Four-function handshower, 1.75 gpm
- 79583 Roughing-in Kit for Deck-Mount Handshowers
- K-23723 Faucet cleaner
- K-27060 18" towel bar
- K-27061 24" towel bar
- K-27062 24" double towel bar
- K-27063 Towel ring
- K-27064 Vertical toilet paper holder
- K-27065 Pivoting toilet paper holder
- K-27069 Robe hook
- K-27128 Toilet paper holder with tray
- K-21335-G Round two-function handshower, 1.75 gpm
- K-27017 Deck-mount bath spout with Straight design
- K-27016 Deck-mount bath spout with Cane design
- K-27019-4 Deck-mount bath faucet handle
- K-27018-3 Deck-mount bath faucet handles with Cross design
- K-27018-4 Deck-mount bath faucet handles with Lever design

Included Components

- GP78825 Polished Chrome hose kit



Codes/Standards










ASME A112.18.1/CSA B125.1
IAPMO Certification


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	BMB	Matte Black with Moderne Brass
	TT	Vibrant Titanium



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)