

## Features

- Rounded glass shades connect with tube attachments and metal bases in contemporary designs fit for any room
- Coordinates with faucets and accessories in the Purist collection
- Requires two bulbs with medium (E26) base; T10 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware

## Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes



## Codes/Standards

UL 1598  
CSA C22.2 No. 250.0


## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SNL	Polished Nickel
	TTL	Titanium
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass
	AFL	French Gold
	BVL	Brushed Bronze



## Required Electrical Service

One circuit required.

120 V, 1 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Steel, Glass  
 Number of Lights: 2  
 Lighting Type: Socket-based  
 Socket Type: E-26 Medium  
 Number of Shades: 2  
 Shade Type: Glass - clear  
 Hanging Type: Non-hanging