

Features

- Rounded glass shades connect with tube attachments and metal bases in contemporary designs fit for any room
- Integrated LED
- Coordinates with faucets and accessories in the Purist collection
- Suitable for damp locations, per UL 1598
- Includes installation hardware

Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes



Codes/Standards


California Energy Commission (CEC)
UL 1598
CSA C22.2 No. 250.0
CA Title 24 JA8



KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	BLL	Matte Black
	2GL	Brushed Moderne Brass



Required Electrical Service

One circuit required.

Lights: 120 V, 0.334 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum, Glass, Plastic

Number of Lights: 1

Lighting Type: Integrated LED

Number of Shades: 1

Shade Type: Glass - clear

Hanging Type: Downrod

Downrod Detail: 2 x 3" (76 mm), 2 x 6" (152 mm), 2 x 12" (305 mm), 4 x 18" (457 mm)

Height: 16-1/16" (408 mm) - 70-1/16" (1780 mm)

Electrical component rating: LED: 40 W, 2875 Lumens, 3000K