

## Features

- Scalloped metal details are juxtaposed against a delicate matte ribbed glass shade for dramatic elegance
- A great piece for almost any space — master bathroom, guest bathroom, hallway, or bedside
- Candelabra base (E12) socket, works best with B10 or B11 bulb (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

## Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




## Codes/Standards

UL 1598  
CSA C22.2 No. 250.0

## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



## Required Electrical Service

One circuit required.

120 V, 0.333 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Steel, Brass, Glass

Number of Lights: 1

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 1

Shade Type: Glass - frosted

Hanging Type: Non-hanging