

Features

- Scalloped metal details are juxtaposed against a delicate matte ribbed glass shade for dramatic elegance
- A great piece for almost any space — master bathroom, guest bathroom, hallway, or bedside
- Requires three medium base (E26) light bulbs (sold separately); works best with A19 bulbs
- Suitable for damp locations, per UL 1598
- Includes installation hardware

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

120 V, 1.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

| | |
|-------------------|---|
| Material: | Steel, Brass, Glass |
| Number of Lights: | 3 |
| Lighting Type: | Socket-based |
| Socket Type: | E-26 Medium |
| Number of Shades: | 1 |
| Shade Type: | Glass - frosted |
| Hanging Type: | Chain |
| Height: | $31\text{-}7/16"$ (798 mm) - $103\text{-}7/16"$ (2627 mm) |