

Features

- Scalloped metal center with orb accents is surrounded by candlestick fixtures and delicate matte ribbed glass shades for dramatic elegance
- A great piece for almost any space — especially in a foyer or dining room
- Candelabra base (E12) socket, works best with B10 or B11 bulb (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs



Material


- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

120 V, 3 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material:	Steel, Brass, Glass
Number of Lights:	6
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	6
Shade Type:	Glass - frosted
Hanging Type:	Chain
Height:	$33\text{-}7/16"$ (849 mm) - $105\text{-}7/16"$ (2678 mm)