

Features

- Uniquely shaped glass shades intersect with decorative metal rings and rods in equestrian-inspired designs
- A great piece for almost any space — especially in a foyer or dining room
- Requires five bulbs with candelabra (E12) base; B11 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

120 V, 2.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material:	Steel, Brass, Glass
Number of Lights:	5
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	1
Shade Type:	Slotted Glass
Hanging Type:	Chain
Height:	38-3/4" (984 mm) - 110-3/4" (2813 mm)