

Features

- Uniquely shaped glass shades intersect with decorative metal rings and rods in equestrian-inspired designs
- A great piece for almost any space — especially in a foyer or dining room
- Requires six bulbs with candelabra (E12) base; type B bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

120 V, 3 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material:	Steel, Brass, Polyester
Number of Lights:	6
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	6
Shade Type:	Fabric
Hanging Type:	Chain
Height:	28-1/8" (714 mm) - 100-1/8" (2543 mm)