

Parohn® | K-27862-CH04

26" chandelier

Features

- Dramatic tapered fabric shades with metal trim and decorative sphere motif create a beautiful accent for interior spaces
- Modernist references are reinterpreted to create a timeless design that works in a range of interior styles and settings
- This collection is at home in modern and traditional interiors
- A great piece for almost any space — especially in a foyer or dining room
- Candelabra base (E12) socket, works best with clear or frosted LED candelabra type B bulbs (sold separately)
- Suitable for damp locations, per UL 1598
- Fixture is dimmable when paired with dimmer switch and compatible bulbs



Codes/Standards

CSA C22.2 No. 250.0

Technical Information

All product dimensions are nominal.

Number of Lights:	4
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	4
Hanging Type:	Chain
Height:	32-15/16" (837 mm) - 101-7/8" (2587 mm)

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One dedicated circuit required.

Lights: 120 V, 2 A, 60 Hz

Electrical Component Ratings


Socket Rating: 60 Hz, 60 W

Warranty

See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty





Installation Notes

Install this product according to the installation instructions.

