

Features

- Dramatic tapered fabric shades with metal trim and decorative sphere motif create a beautiful accent for interior spaces
- Modernist references are reinterpreted to create a timeless design that works in a range of interior styles and settings
- This collection is at home in modern and traditional interiors
- A great piece for almost any space — especially in a foyer or dining room
- Candelabra base (E12) socket, works best with clear or frosted LED candelabra type B bulbs (sold separately)
- Suitable for damp locations, per UL 1598

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes





Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One dedicated circuit required.

Lights: 120 V, 4 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Brass

Number of Lights: 8

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 8

Shade Type: Fabric

Hanging Type: Chain

Height: $39\text{-}7/8''$ (1013 mm) - $109''$ (2768 mm)

Electrical component Socket Rating: 60 Hz, 60 W
rating: