

Features

- A combination of simple, elegant forms, and its pivoting shade reinterprets timeless Art Deco style for a modern setting
- Dome-shaped metal shade that pivots so you can direct the lamp's illumination in almost any direction
- This collection is at home in primarily modern interiors
- A great piece for almost any space — master bathroom, guest bathroom, hallway, or bedside
- Candelabra base (E12) socket, works best with clear or frosted candelabra type G bulbs (sold separately)
- Suitable for damp locations, per UL 1598

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One dedicated circuit required.

120 V, 0.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum, Brass

Number of Lights: 1

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 1

Shade Type: Metal

Hanging Type: Non-hanging