

Features

- A combination of simple, elegant forms, and its pivoting shade reinterprets timeless Art Deco style for a modern setting
- Dome-shaped metal shade that pivots so you can direct the lamp's illumination in almost any direction
- This collection is at home in primarily modern interiors
- A great piece for almost any space — perfect over a large island or dining table
- Candelabra base (E12) socket, works best with clear or frosted candelabra type G bulbs (sold separately)
- Suitable for damp locations, per UL 1598

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One dedicated circuit required.

Lights: 120 V, 4 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum, Brass

Number of Lights: 8

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 8

Shade Type: Metal

Hanging Type: Chain

Height: $28\text{-}1/2"$ (724 mm) - $97\text{-}3/8"$ (2474 mm)

Electrical component rating: Socket Rating: 60 Hz, 60 W