



Spacity™

One-piece compact elongated toilet with skirted trapway

K-28020IN-S

Features

- Compact, streamlined one-piece toilet
- Compact elongated bowl offers added comfort while requiring less space
- Rim-to-floor height: 15-1/4" (400 mm)
- Dual-flush offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- Left-hand Polished Chrome trip lever
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Quiet-Close™ elongated lid and seat prevents slamming
- Quick-Attach™ hardware for fast and secure installation
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Coordinates with other products in the Spacity™ collection

Material

- Vitreous china

Installation

- Standard 12" (305 mm) rough-in
- Supply line sold separately



Codes/Standards

None Applicable

KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Compact elongated
Flush type:	Revolution 360, AquaPiston
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-3/8" (163 mm)

Notes

Install this product according to the installation instructions.