

KOHLER®


Spacity™
One-piece compact elongated toilet with skirted
trapway, dual-flush
K-28020MY-S

Features

- Compact, streamlined one-piece toilet
- Compact elongated bowl offers added comfort while requiring less space
- Rim-to-floor height: 15-1/4" (400 mm)
- Left-hand Polished Chrome trip lever
- Dual flush offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Quiet-Close™ elongated lid and seat prevents slamming
- Quick-Attach™ hardware for fast and secure installation
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Coordinates with other products in the Spacity™ collection

Installation

- Standard 12" (305 mm) rough-in
- Supply line sold separately



Codes/Standards

None Applicable

See website for detailed warranty information.

+86-21-2606-2000

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to <http://www.kohlerasiapacific.com>.

12-30-2024 01:30 - MS

THE BOLD LOOK
OF **KOHLER**®

KOHLER®

Spacity™
One-piece compact elongated toilet with skirted
trapway, dual-flush
K-28020MY-S



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Compact elongated
Flush type:	Dual-Flush Technology
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-3/8" (163 mm)

Notes

Install this product according to the installation instructions.