

KOHLER®


Spacity™
Hidden cord one-piece compact elongated toilet with
skirted trapway, dual-flush
K-28020PH-HC

Features

- Compact, streamlined one-piece toilet
- Compact elongated bowl offers added comfort while requiring less space
- Rim-to-floor height: 15-1/4" (400 mm)
- Dual-flush offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- Left-hand Polished Chrome trip lever
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Hidden cord design conceals bidet seat cords (bidet seat sold separately)
- Coordinates with other products in the Spacity™ collection

Installation

- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately



Codes/Standards

None Applicable

See website for detailed warranty information.

+86-21-2606-2000

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to <http://www.kohlerasiapacific.com>.


12-30-2024 01:30 - PH

THE BOLD LOOK
OF **KOHLER®**

KOHLER

Spacity™

Hidden cord one-piece compact elongated toilet with
skirted trapway, dual-flush
K-28020PH-HC



Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount
 Waste Outlet: Floor
 Bowl shape: Compact elongated
 Flush type: Dual-Flush Technology
 Trap passageway: 1-15/16" (49 mm)
 Rim to water surface: 6-3/8" (163 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.