



# Spacity®

One-piece compact elongated toilet with skirted trapway, 1.28 gpf  
**K-28020**

## Features

- Compact, streamlined one-piece toilet
- Compact elongated bowl offers added comfort while requiring less space
- Standard height
- 1.28 gpf (4.8 lpf)
- Left-hand Polished Chrome trip lever
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Quiet-Close™ elongated lid and seat prevents slamming
- Quick-Attach™ hardware for fast and secure installation
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Coordinates with other products in the Spacity™ collection

## Installation

- Standard 12" (305 mm) rough-in



## Codes/Standards

ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)

## KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes


*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------

# KOHLER®

**Spacity®**  
One-piece compact elongated toilet with skirted  
trapway, 1.28 gpf  
**K-28020**



## Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-3/8" (163 mm)
Rough-in:	12" (305 mm)

## Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

10-5-2025 19:37 - US/CA

THE BOLD LOOK  
OF **KOHLER®**