

Features

- Digitally controlled thermostatic mixing valve
- Antiscald protection
- Built-in temperature and flow control
- Allows for two different temperature and flow zones in your shower
- Highly anticipated updates to the KOHLER Konnect™ app will unlock additional Anthem™ system features, Kohler-developed experiences, and system updates
- Up to 22 gpm (83 lpm) flow rate at 45 psi (3.1 bar) with maximum flow of 9.5 gpm (36 lpm) from one outlet
- Four independently controllable G 1/2 female outlets with brass connections
- G 3/4 female inlets with brass connections

Material

- Reinforced engineering-grade thermoplastic body

Installation

- Install valve approximately 32' (9754 mm) away from the digital control (cable supplied with control)
- After digital control is connected to valve and power source, follow on-screen prompts for easy setup; no Internet needed. (Digital control sold separately)

Required Products/Accessories

For wall-mount installation
K-28214 Digital control

Optional Products/Accessories

K-28213 Remote on/off button for digital thermostatic valve




Codes/Standards

ASME A112.18.1/CSA B125.1

KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Thermostatic valve: 120/240 V, 1.6 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Power source: Hardwire - AC, included

Shower Valve:

Flow Rate (Max) @ 45 psi	22.5 gal/min (85.2 l/min)
Manufacturer's minimum rated flow:	0.9 gal/min (3.4 l/min)
Pressure:	45 psi (3.1 bar)
Maximum (Static) Pressure:	125 psi (8.6 bar)
Minimum (Operating) Pressure:	15 psi (1 bar)

Drain included: No

Electrical component rating: Thermostatic valve: 120/240 V, 1.6 A, 50/60 Hz

Cable length: Data, 32 ft (9.8 m)

Bluetooth® range: 33 ft (10.1 m)

1800 103 2244 (Toll Free) & +91-124-4319685 / 86

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.co.in.

9-24-2023 21:14 - IN