

Features

- Digital control with easy-to-read icons and configurable touch screen
- Control temperature, flow, and up to six shower outlets from a simple, intuitive interface
- Turn the large KOHLER® dial for easy temperature and flow rate adjustment
- Nine user-definable presets let you save your favorite shower settings
- Use with the KOHLER Konnect® app to unlock additional Anthem system features, Kohler-developed experiences, and system updates
- System warm-up and pause feature
- Includes optional flow restrictor, limiting total flow to 1.75 gpm (6.6 lpm), for installations where water conservation or CEC compliance is desired
- Features multiple language options
- Connect up to two controls within your digital shower system
- Requires an Anthem digital thermostatic valve (K-28209, K-28210, K-28211 or K-28212); sold separately
- Pair with optional Anthem remote on/off button; sold separately

Material

- Premium material construction for durability and reliability

Installation

- After digital control is connected to valve and power source, follow on-screen prompts for easy setup; no Internet needed
- Wall-mount

Required Products/Accessories

K-28209 Two-port digital thermostatic valve

or

K-28210 Three-port digital thermostatic valve

or

K-28211 Four-port digital thermostatic valve

or

K-28212 Six-port digital thermostatic valve

Recommended Products/Accessories

K-28213 Remote on/off button for digital thermostatic valve



Codes/Standards

UL 1951

CSA C22.2 No. 68


KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	RGD	Vibrant Rose Gold
	BGP	Vibrant Brushed Graphite
	TT	Vibrant Titanium



Technical Information

All product dimensions are nominal.

Spout:

Cable length: Data, 32 ft (9.8 m)

Max. Ambient temp: 120°F (48.9°C)

Notes

Install this product according to the installation instructions.