



ModernLife™

The Complete Solution™ one-piece toilet with skirted trapway, dual-flush
K-28220T-SL

Features


- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Rim-to-floor height: 15-1/4" (400 mm)
- Rimless design makes toilet bowl more hygienic and easier to clean
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Dual flush offers a choice of 0.8 or 1.28 gpf (3.0 or 4.5 lpf)
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Slim seat included
- Quiet-Close™ lid and seat prevents slamming
- LED nightlight provides improved visibility in low-light conditions
- Integrated freshener fills air with a light, subtle scent for up to 1 month (replaceable scent pack)
- The Complete Solution toilets provide everything you need, including bowl, tank, seat, wax ring, supply line, and hardware

Material

- Vitreous china

Installation

- Standard 12" (305 mm) rough-in



Codes/Standards

Plumbing Standards

GB 25502


GB/T 6952


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Round
Flush type:	Revolution 360, AquaPiston
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-1/8" (156 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.