

Components®

Pull-down kitchen sink faucet with two-function sprayhead K-28269

Features

- Two-function pull-down sprayhead with touch control allows you to switch between aerated and Sweep® sprays
- Sweep[®] spray features specially angled nozzles that form a wide, powerful blade of water to sweep your dishes and sink clean
- DockNetik[®] secure docking system locks sprayhead into place when not in use
- ProMotion® technology's light, quiet braided hose and swiveling ball joint make the pull-down sprayhead easier and more comfortable to use
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- High-arch spout offers vertical clearance for tall cookware and pitchers
- Single lever handle makes adjusting water temperature easy with one hand
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- For single-hole or three-hole installation (escutcheon plate sold separately)
- Flexible supply lines simplify installation

Recommended Products/Accessories

K-23723 Faucet cleaner

Optional Products/Accessories

K-24461 Three-hole kitchen faucet escutcheon





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651

KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

CP	Polished Chrome
SN	Vibrant® Polished Nickel
AF	Vibrant® French Gold
VS	Vibrant® Stainless
BV	Vibrant® Brushed Bronze
BL	Matte Black
2MB	Vibrant® Brushed Moderne Brass
BMB	Matte Black with Moderne Brass
ТТ	Vibrant Titanium

1-800-4KOHLER (1-800-456-4537)


Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to <u>www.kohler.com</u> USA or <u>www.kohler.ca</u> Canada 12-17-2024 01:24 - US/CA



Components®

KOHLER, Faucets

Pull-down kitchen sink faucet with two-function sprayhead K-28269



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Drain included:

No

Spout: Spout reach: 9-11/16" (246 mm)

Handshower:

Rated maximum flow:

0 gal/min (0 l/min)

Notes

Install this product according to the installation guide.

ADA compliant for faucet handles only. ADA compliant for faucet handles only ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

