

Features

- Fits minimum 36" (914 mm) apron sink base cabinet
- Single bowl
- 8" (203 mm) depth
- Integral apron
- Sink drain with strainer sold separately
- No faucet holes; requires wall- or counter-mount faucet

Material

- KOHLER® enameled cast iron
- Acid-resistant enamel finish

Installation

- Undermount

Recommended Products/Accessories

- K-6062 Sink rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap



Codes/Standards




ASME A112.19.1/CSA B45.2
IAPMO Certification


KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|--------------|
|  | 0 | White |
|  | 96 | Biscuit |
|  | 7 | Black Black™ |



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Center(s): 8" (203 mm)

Min. base cabinet width: 36" (914 mm)

Bowl area (Only):
 Length: 29-1/2" (749 mm)
 Width: 15-3/8" (390 mm)
 Bowl depth: 8-5/8" (220 mm)
 Water depth: 8" (203 mm)

Drain hole: 3-5/8" (92 mm)

Template: Apron-front, 1463896-7, required, included
 Cabinet, 1465115-7, required, included

Notes

Install this product according to the installation instructions.