

Features

- Multifunction handshower with advanced spray engine provides two spray experiences: full coverage and Microbubble
- Easily transition between sprays with control buttons on sprayface
- Handle extends with the push of a button for washing hard-to-reach areas
- 2.5 gpm (9.5 lpm) maximum flow rate
- Pairs with the K-28683T SpaViva™ grooming device via magnetic connection (sold separately)
- Requires shower hose (sold separately)

Material

- Plastic construction
- KOHLER® finishes resist corrosion and tarnishing

Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- G 1/2 inlet connection



Codes/Standards



Plumbing Standards
GB/T 23447

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Notes

For use with automatic compensating valves rated at 1.5 gal/min (5.7 l/min) or less.

Install this product according to the installation guide.