



Man's Lav™

Undermount bathroom sink
K-2885-8U

Features

- 8" (203 mm) centerset faucet holes.
- Sloped rectangular basin.
- Overflow drain.
- Can accommodate single-hole center-mount or widespread faucet.
- 24" (610 mm) x 13" (330 mm)

Material

- KOHLER® enameled cast iron.

Installation

- Undermount.

Recommended Products/Accessories

K-8998 P-Trap
K-23726 Drain treatment
K-23725 Cast iron cleaner

Included Components

Additional Components:
1193643 Basin clamps



ADA

CSA B651

Codes/Standards

ASME A112.19.1/CSA B45.2
ADA
ICC/ANSI A117.1
CSA B651

KOHLER® Cast Iron Components Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.



Color	Code	Description
	0	White
	96	Biscuit
	95	Ice™ Grey
	KA	Black 'n Tan

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current Specification Sheet, go to www.kohler.com.

5-1-2020 06:11 - US/CA

THE BOLD LOOK
OF **KOHLER**®



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Undermount

Bowl area (Only): Length: 24" (610 mm)
Width: 13" (330 mm)
Water depth: 4-1/4" (108 mm)

Number of deck holes: 3

Faucet hole spacing: 8" (203 mm)

Faucet hole(s): 2-3/8" (60 mm)

Drain hole: 1-3/4" (44 mm)

Template: 114408-7, required, included

Notes

Install this product according to the installation instructions.

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.