

Features


- Deep rectangular basin with a contemporary design minimizes splash
- Rear drain placement increases vanity cabinet storage space underneath sink
- Unique front slotted overflow creates a sleek look
- Glazed finish is easy to clean
- No faucet holes; requires wall- or counter-mount faucet
- Includes drain plug cap
- Coordinates with Spacity™ vanities (sold separately)

Material

- Vitreous china

Installation


- Undermount



Codes/Standards

Plumbing Standards
GB/T 6952

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Min. base cabinet width: 19-1/16" (485 mm)

Bowl area (Basin #1):
 Length: 13-11/16" (347 mm)
 Width: 9-15/16" (252 mm)
 Bowl depth: 4-5/16" (110 mm)
 Water depth: 3-1/8" (80 mm)

With overflow: Yes

Drain hole: 1-3/4" (45 mm)

Notes

Install this product according to the installation instructions.

Install this product according to the installation instructions.