Bellera™ | K-29108

Touchless pull-down kitchen sink faucet with three-function sprayhead

Features

- Touchless on/off with a wave of your hand or an object such as a pan
- Response® technology uses a state-of-the-art motion sensor for reliable touchless activation
- LED light indicates Response® is ready to use
- AC-powered operation—no batteries to replace
- Three-function pull-down sprayhead with touch-control allows you to switch between stream, Sweep® spray and Boost technology
- Sweep® spray features specially angled nozzles that form a wide, powerful blade of water to sweep your dishes and sink clean
- Boost technology increases the flow rate by 30% with the press of a button. Use Boost with stream for faster filling or with Sweep® spray for more powerful cleaning
- DockNetik® secure docking system locks sprayhead into place when not in use
- ProMotion® technology's light, quiet braided hose and swiveling ball joint make the pull-down sprayhead easier and more comfortable to use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- High-arch spout offers vertical clearance for tall cookware and pitchers
- Single lever handle makes adjusting water temperature easy with one hand
- Handle rotates 90° forward to prevent contact with backsplash
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)



Sustainability

WATER-SAVING DESIGN

Available Colors/Finishes

Color tiles intended for reference only.

	CP	Polished Chrome
	VS	Vibrant Stainless

+001-800-456-4537
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to la.kohler.com/en for Mexico/Latin America or www.kohler.com USA.
11-03-2026 19:01 - LM

THE BOLD LOOK OF KOHLER.

Codes/Standards

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651

Technical Information

All product dimensions are nominal.

Handle

Handle Style/Type:	Lever

Spout

Spout Reach:	9" (228 mm)

Flow Rate

Faucet Flow Rate:	1.5 gpm (5.7 l/min)

Valves

Included Valves:	Ceramic disc, Thermostatic Mixer

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Recommended Products/Accessories

- K-23723 Faucet cleaner

Optional Products/Accessories

- 1012715 Deep Rough-In


Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty

+001-800-456-4537
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to la.kohler.com/en for Mexico/Latin America or www.kohler.com USA.
11-03-2026 19:01 - LM

THE BOLD LOOK OF KOHLER.



Installation

- Requires nonswitched undercounter outlet
- Single-hole or three-hole installation (escutcheon plate included)
- Flexible supply lines simplify installation

Installation Notes

Install this product according to the installation instructions.

REQUIRED: Unswitched power outlet (120 V AC) located below the sink and within 5' (1.5 m) of the control box. (Garbage disposals typically use switched outlets and are not recommended.)
ADA complaint for faucet handles only.
ADA compliant for faucet handles only
ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

+001-800-456-4537
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to la.kohler.com/en for Mexico/Latin America or www.kohler.com USA.
11-03-2026 19:01 - LM

THE BOLD LOOK OF KOHLER.