

Features

- The Arendela collection has a light, airy quality and is a beautiful accent for any space
- The delicate metal framework of the fixture suspends Arendela's briolette faceted disks, which sparkle and throw reflections from all angles as they catch the light
- A perfect complement to the KOHLER Briolette glass vessel sink
- Candelabra base (E12) socket, works best with clear or frosted LED candelabra type B bulbs (sold separately)
- Suitable for damp locations, per UL 1598

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes



Codes/Standards


UL 1598
CSA C22.2 No. 250.0


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SNL	Polished Nickel
	BNL	Brushed Nickel
	CPL	Polished Chrome
	2GL	Brushed Moderne Brass



Required Electrical Service

One dedicated circuit required.

Lights: 120 V, 1.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum, Zinc, Glass

Number of Lights: 3

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 3

Shade Type: Glass - clear

Hanging Type: Non-hanging

Electrical component Socket Rating: 60 Hz, 60 W
rating: