

## Features

- The Arendela collection has a light, airy quality and is a beautiful accent for any space
- The delicate metal framework of the fixture suspends Arendela's briolette faceted disks, which sparkle and throw reflections from all angles as they catch the light
- A perfect complement to the KOHLER Briolette glass vessel sink
- Candelabra base (E12) socket, works best with clear or frosted LED candelabra type B bulbs (sold separately)

## Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




## Codes/Standards

UL 1598  
CSA C22.2 No. 250.0

## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



## Required Electrical Service

One dedicated circuit required.

Lights: 120 V, 3 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum, Zinc, Glass

Number of Lights: 6

Lighting Type: Socket-based

Socket Type: E-12 Candelabra

Number of Shades: 6

Shade Type: Glass - clear

Hanging Type: Chain

Height: 19-3/4" (501 mm) -  
89-15/16" (2285 mm)

Electrical component rating: Socket Rating: 60 Hz, 60 W