

**Features**


- Single handle provides on/off activation, volume, and temperature control
- Tall height is ideal for vessel-style sinks
- 7-4/5" (200 mm) spout height
- 6-5/8" (168 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coin aerator is easy to remove for maintenance
- Includes clicker drain

**Material**

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

**Installation**

- Single hole
- Supply lines included

**Codes/Standards**

Plumbing Standards  
TIS 2067-2552


See website for detailed warranty information.

**Available Colors/Finishes**

*Color tiles intended for reference only.*

**Color Code Description**

	CP	Polished Chrome
---	----	-----------------



**Technical Information**

All product dimensions are nominal.

**Faucet:**

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

**Notes**

Install this product according to the installation guide.