

Features


- Single handle provides on/off activation and volume control
- For use with cold water line only
- Tall height is ideal for vessel-style sinks
- 7-4/5" (200 mm) spout height
- 6-5/8" (168 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coin aerator is easy to remove for maintenance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Single hole
- Supply lines included



Codes/Standards


None Applicable

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: No

Drain with overflow: No

Notes

Install this product according to the installation guide.