



Persuade® Curv

Vanity-top centerset bathroom sink

K-2956-4

Features

- 4" (102 mm) centerset faucet holes.
- Basin with square back and curved front.
- Overflow drain.
- Combines with industry-standard 24-inch vanities.
- Coordinates with other products in the Persuade collection.

Material

- Vitreous china.

Installation

- Vanity-top.

Recommended Products/Accessories

K-8998 P-Trap
K-2529 Vanity
K-2526 Console Table
K-2527 Petite Vanity
K-23726 Drain treatment
K-23725 Cast iron cleaner



Codes/Standards

ASME A112.19.2/CSA B45.1

KOHLER® One-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
	HW1	Honed White
	96	Biscuit



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Vanity top/ITB

Bowl area (Only): Length: 18-13/16\" (478 mm)
Width: 13-7/8\" (352 mm)
Water depth: 2-1/2\" (64 mm)

Number of deck holes: 3

Faucet hole spacing: 4\" (102 mm)

Faucet hole(s): 1-1/4\" (32 mm)

Drain hole: 1-3/4\" (44 mm)

Template: 1139967-7, required, included

Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when incorrect cut-out template is used.

NOTE: This bathroom sink is also designed for installation to the K-2526, K-2527 and K-2529 vanities.