



Persuade® Curv
Vanity-top centerset bathroom sink
K-2956-4

Features

- 4" (102 mm) centerset faucet holes
- Basin with square back and curved front
- Overflow drain

Material

- Vitreous china

Installation

- Vanity top

Recommended Products/Accessories

K-8998 P-Trap
K-23726 Drain treatment
K-23725 Cast iron cleaner



Codes/Standards


ASME A112.19.2/CSA B45.1

**KOHLER® One-Year Limited
Warranty**

See website for detailed warranty information.



Persuade® Curv
Vanity-top centerset bathroom sink
K-2956-4



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Bowl area (Only):	Length: 18-13/16" (478 mm) Width: 13-7/8" (352 mm) Water depth: 2-1/2" (64 mm)
Number of deck holes:	3
Faucet hole(s):	1-1/4" (32 mm)
Drain hole:	1-3/4" (44 mm)
Template:	1139967-7, required, included

Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when incorrect cut-out template is used.

NOTE: This bathroom sink is also designed for installation to the K-2526, K-2527 and K-2529 vanities.