

Features


- 36" (914 mm) minimum base cabinet width
- Single bowl
- Rectangular bowl
- Rounded 3/8" (10 mm) corners are easy to clean
- Beveled cone-shape bowl slopes into drain, easily disposing debris
- 7-1/2" (190 mm) depth provides generous workspace
- SilentShield™ sound-absorption technology offers quieter performance
- Single faucet hole with one accessory hole to the right
- 3-27/32" (98 mm) drain opening
- Center drain and overflow
- With overflow cover
- Accessories stack and slide on sink's beveled edge to enhance food prep and cleanup
- Three-piece nested colander for in-sink rinsing and draining
- Sink strainer keeps large items from passing into the drain

Material

- KOHLER stainless steel sinks resist corrosion and tarnishing

Installation

- Top-mount or undermount
- Installation hardware included




Codes/Standards

None Applicable

See website for detailed warranty information.



Ladena™
630 mm top-/undermount single-bowl kitchen sink
with accessories
K-29791T-2HD



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 24-13/16" (630 mm)

Number of deck holes: 2

Notes

Install this product according to the installation instructions.