



Tresham®
Drop-in Bathroom Sink
K-2992-4

Features

- 4" (102 mm) centerset faucet holes
- Oval basin with raised rim
- Overflow drain
- Coordinates with other products in the Tresham collection

Material

- Vitreous china
- Vitreous china

Installation

- Drop-in

Recommended Products/Accessories

K-8998 P-Trap
K-23726 Drain treatment
K-23725 Cast iron cleaner



Codes/Standards



ASME A112.19.2/CSA B45.1

**KOHLER® One-Year Limited
Warranty**

See website for detailed warranty information.





Tresham®
Drop-in Bathroom Sink
K-2992-4



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Bowl area (Only):	Length: 20-1/16" (510 mm) Width: 11-15/16" (303 mm) Water depth: 6-1/16" (154 mm)
With overflow:	Yes
Number of deck holes:	3
Faucet hole(s):	1-1/4" (32 mm)
Drain hole:	1-3/4" (44 mm)
Template:	1162720-7, required, included



Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.