

Features


- Single Lever handle provides on/off activation and volume control
- For use with cold water line only
- 3-11/16" (94 mm) spout height
- 4-1/2" (114 mm) spout reach
- 1.4 gpm (5.2 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Drain sold separately
- Includes installation hardware

Material

- Brass construction ensures durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- Single-hole installation


**Codes/Standards**

Plumbing Standards
TIS 2067-2552

See website for detailed warranty information.

KOHLER® Faucets

Fore Line™
Single-handle bathroom sink faucet, cold only, 5.2
lpm
K-30055T-4CD



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.37 gal/min (5.2 l/min)

Drain with overflow: Yes

Drain tailpiece included: No

Spout:

Spout reach: 4-1/2" (115 mm)

Notes

Install this product according to the installation guide.