

KOHLER® Faucets

Accliv™

Touchless single-hole lavatory faucet, cold only, 0.98 lpm

K-30276T-S5

Features


- Electronic infrared (TOF) sensor for accurate activation
- On-demand usage with 60-second max. continual run cycle to prevent vandalism and save water
- Design-forward aesthetic for commercial bathroom spaces
- Vandal-resistant aerator
- 4" (102 mm) spout reach
- 3-5/8" (92 mm) spout height
- Aerated flow
- For use with cold water line only
- 0.26 gpm (0.98 lpm) maximum flow rate at 60 psi (4.14 bar)
- Below-counter valving reduces the faucet footprint and provides easier service
- Includes spout assembly, control box assembly, aerator key, and standard installation hardware

Material

- Premium metal construction for durability and reliability

Installation

- Single-hole installation
- Deck-mount
- Requires AC or DC power unit (sold separately)
- Mechanical mixer and mixing valve sold separately



Codes/Standards


None Applicable

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

Notes

Install this product according to the installation instructions.