

Features

- Audio amplifier with BLUETOOTH® connectivity for wireless streaming of audio input
- Reads your music or audio selections from any device enabled with BLUETOOTH® wireless technology
- Best-in-class audio with sound by Harman Kardon®
- Designed for use with the Anthem+™ digital shower system, but can also be used as a standalone amplifier enabled with BLUETOOTH® wireless technology
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet (10 meters) away
- Includes SD Card with Kohler-curated spa music, in partnership with Myndstream®
- Connects with up to four SoundTile® water-resistant speakers (or any standard 4- or 8-ohm speakers)
- User definable device name and PIN code option when used with Anthem+™ digital system
- Standby mode
- Two 1/7" (4 mm) input jacks for wired audio input
- One 1/7" (4 mm) line out jack
- One port for connection to Anthem+™ system controller
- One jack for power cord connection
- Screw terminal block for two to four speakers

Material

- Premium material construction for durability and reliability

Technology

- The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license

Installation

- Supplied with rubber feet for locating on a countertop or shelf or can be wall mounted (mounting bracket and screws included)

Recommended Products/Accessories








Codes/Standards

None Applicable

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.



Required Electrical Service

One circuit required.

Amplifier module: 120 V, 60 Hz

Technical Information

All product dimensions are nominal.

Power source: Plug - AC, not included

Amplifier channels: 1 at 40 W per channel

Spout:

Minimum impedance: 3 Ohms

Bluetooth® range: 33 ft (10.1 m)

Bluetooth® version: 5.3

Max. Ambient temp: 104°F (40°C)

Max. Relative humidity non-condensing: 90%

Output power: 40 Watts x 1 into 3 Ohms

Frequency response: 20 Hz - 18 kHz +/-

Notes

Install this product according to the installation instructions.